

Lime Dosing

Bin Activators BA

10



Description ▼

The BA Bin Activator is a device of tapered conical shape that due to vibration facilitates material flow from hoppers or silos. It consists of a seamless carbon or stainless steel cone manufactured on a sheet metal lathe, a seamless SINT® engineering polymer seal with integrated upper and lower flange, suspensions for connection with the silo, as well as one or two electric vibrators.

Function ▼

One or two electric vibrators fitted to the unit generate vibration of the Bin Activator every time the feeding device beneath the silo is started for material extraction. During operation the Bin Activator describes a gyratory movement which is transmitted to the material inside the silo. The result is smooth material flow through the Bin Activator outlet into the downstream feeder.

BA Bin Activators are used in various applications to facilitate discharging of powdery materials from silos or hoppers. The use of this equipment ensures optimum feeding of the material causing "mass flow" inside the silo, thus avoiding bridging or rat holing phenomena.



Application ▼

Discharging of lime from silo.

The BA outlet is usually shut off by a rotary valve, slide valve or butterfly valve which is connected with a downstream screw conveyor or micro-batch feeder.

Benefits ▼

- ✓ No material residue thanks to appropriate design features;
- ✓ High resistance to corrosion with stainless steel version;
- ✓ High discharging performance;
- ✓ Reduced maintenance thanks to long-life seal material.


Lime Dosing Bin Activators BA



Technical Features / Performance ▼

- ▶ Diameters up to 2,350mm (8 ft)
- ▶ Fabricated parts available in 304L and 316 stainless steel
- ▶ No internal residue deadspace
- ▶ Suspensions suitable for positive or negative pressure silo filling
- ▶ Construction material: carbon or stainless steel
- ▶ Vibrating outlet cone fitted with outlet opening hatchway

Overall Dimensions ▼



TYPE	Size	Ø A* Standard	B	C	H	Motovibrators	kg
BA040	400	114	380	427	330	1	59
BA060	600	168	580	519	408	1	80
BA075	750	219	730	609	456	1	99
BA090	900	219	880	684	531	1	134
BA100	1,000	273	980	734	555	1	146
BA125	1,250	273	1,230	937	730	1	290
BA150	1,500	323	1,480	1,120	774	1	475
BA180	1,800	323	1,780	1,194	924	2	726
BA210	2,100	406	2,080	1,420	1,033	2	881
BA235	2,350	406	2,330	1,547	1,166	2	1,255
BA250	2,500	406	2,480	1,705	1,307	2	1,530
BA300	3,000	406	2,980	1,955	1,568	2	2,456

* Further outlet dimensions reported in Technical Catalogue

Dimensions in mm

This datasheet does not show the complete range but only the models most suitable for the application.